


PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN


Overall



PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN


Vacuum Chamber



PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN


Lid



PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN


Hinge



PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN


Air Valve



PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN


Sealbeam



PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN


4m³ Transformer



PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN


8m³ Transformer



PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN

Control Panel



PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN

Overall

Item No.	Description	Position	Item No.	Description	Position	Item No.	Description	Position
15884	Sealbeam Standard Compact Complete for 59006	4	AI831	Clamping Plate Pump T1 T2-4m3 for 59006	19	65749	M6 Hex Nut Din 985 for 59006	40
27791	Net Entree Male Snap-In STF42 for 59006	5	AI832	Square Hose Coupling 3 8"x8 Ext. for 59006	22	65836	Hucknagel Magna-Lok MGLP-B6-4 for 59006	41
30022	Thermal Fuse 8A for 59006	6	AI833	Cover Back Side T2 for 59006	23	27782	Hexagon Flangenut M5 Din 6923 A2 for 59006	42
30014	Vacuum Pump 004-316 220/240-1-50/60 for 59006	7A	AI834	Filler Plate Bottom T2 - R2 for 59006	28	27789	Slott. Rais. Counter. Head Screw M4x10 Din7985 A2 for 59006	43
AI827	Vacuum Pump 008 220 240-1-50 60 for 59006	7B	AI835	Filler Plate Top T2 - R2 for 59006	29	35041	Hose Clip Klemfa 12.8x14.8mm for 59006	44
15791	Combi-Trafo P100/230V-S16/24V for 59006	9	AI836	Chassis T2 for 59006	31	27781	Hexagon Flangenut M6 Din6923 A2 for 59006	48
AI828	Din Rail B 1 Fase for 59006	10A	AI837	M8 Hexagon Cap Nut DIN 917 for 59006	32	AI841	Suction Hose T2 for 59006	49
AI829	Din Rail A 1 Fase for 59006	10B	AI838	M8x35 Hexagon Socket Set Screw Din 916 for 59006	33	63991	Non-Return Valve 8mm for 59006	51
35476	Square Hose Coupling 1/4x8 Ext. for 59006	11	AI839	Locking Plate Hinge for 59006	34	30019	Hose Clip Klemfa 12.8x14.8mm for 59006	52
AI830	Baseplate T2 for 59006	16	AI840	Lid Locker T2 for 59006	37	AI842	Cap Holder 04-Control Mini for 59006	53
65834	Vibration Absorber D=25 H=17 M6x10 for 59006	17	27787	Hexagon Screw M6x16 DIN933 A2 for 59006	39			

Vacuum Chamber

Item No.	Description	Position	Item No.	Description	Position	Item No.	Description	Position
AI843	Vacuum Chamber T2-R2 for 59006	1	AI846	M5 Hexagon Cap Nut Din 917 for 59006	6	27810	Spring Ring with Cover 6mm / Shaft Locker with Cover for 59006	11
AI844	Seal Cylinder for 59006	2	35852	O-Ring 28x3 for 59006	7	AI850	M3x16 Cross Recessed Raised Cheese Head Screws - Din 7985 for 59006	12
AI845	Seal Wire C1 for 59006	3	AI847	Comb. Valve Model-II for 59006	8	15775	Micro Switch MV3003L for 59006	13
65776	Spring Washer Din 127 - A4 for 59006	4	AI848	Hinge T2 Assembled for 59006	9	65772	M3 Washer DIN 9021 for 59006	14
27830	Slotted Cheese Head Screw M4x6 A2 Din84 for 59006	5	AI849	Pivot T2 for 59006	10	27823	Hexagon Nut M3 Din934 A2 for 59006	15

PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN

Lid

Item No.	Description	Position	Item No.	Description	Position	Item No.	Description	Position
AH261	T2 Vacuum Cover Dome for 59006	1	AI851	Silicon Bar T2 for 59006	3	15842	Silicone T-Profile 40 Shore One Meter for 59006	5
35105	Sil.Profile Lidgasket 8mm 60 SH/25mtr for 59006	2	62750	Acrylic Tape Double Sided 25mm L60mm for 59006	4	65761	Clamping Spring Silicone Holder for 59006	6

Hinge

Item No.	Description	Position	Item No.	Description	Position	Item No.	Description	Position
AI852	Hinge T2 for 59006	1	AI853	Locking Plate Hinge Part for 59006	3	AI855	Gas Spring 0814MF 350N for 59006	5
35093	Guide Bearing 6x9x6 for 59006	2	AI854	Spacer 6.2x10x7.5 for 59006	4	27814	Hexagon Nut M8 Din934 A2 for 59006	7

Air Valve

Item No.	Description	Position	Item No.	Description	Position	Item No.	Description	Position
AI856	Base Block Combination Valve Model II for 59006	1	AI859	O-Ring 12x2mm for 59006	6	27816	Adj.Screw/Soc.Head M5x16 Din916 A2 for 59006	10
AI857	Adapter Valve 6mm for 59006	2	AI860	Right Hose Coupling 1.8"x4 Ext. for 59006	7	AI666	3-2 Armature Met 8mm Seal for 59006	12
35402	Square Hose Coupling 1/8x4 Ext. for 59006	3	AI861	Clamping Plate Valve Armature for 59006	8	AH174	Coil 24Vac 50/60HZ 8.5VA for 59006	13
AI858	Adapter Valve 2.5mm for 59006	5	35261	Brass Hose Coupling 1/4x8 Ext. for 59006	9	35852	O-Ring 28x3 for 59006	14

Sealbeam

Item No.	Description	Position	Item No.	Description	Position	Item No.	Description	Position
AI862	Sealbeam Compact Mini Maxi for 59006	1	AI864	Slotted Cheese Head Screw for 59006	3	AI866	Teflon Tape EN 40mm for 59006	5
AI863	Compression Spring Seal Beam for 59006	2	AI865	Adj.Screw Soc.Head M8x16 D915 for 59006	4	AI867	Seal Wire 3.5x0.3mm L=1mtr for 59006	6

PARTS BREAKDOWN

ITEM	MODEL
59006	VP-NL-0004-SN

4m³ Tranformer

Item No.	Description	Position	Item No.	Description	Position	Item No.	Description	Position
AC744	Rail JMV35SL 7 Hole 173mm for 59006	1	65708	Locking Plate Zap ZDU 6-2 for 59006	5	35323	End Plate Wire Connector for 59006	10
35305	End Fent for 59006	2	35306	Fuse Clamp 2.5-2/ZSI for 59006	7	35315	Double Clamp 2.5-2 for 59006	11
AI868	Mas AB100-K09KJ400 MS4P 24V 50/60Hz for 59006	3	15818	Fuse 5x20 4A Slow for 59006	8			
15772	Contactor 24VAC for 59006	4	35307	Fuse Keram.5x20 2.5A Delay for 59006	9			

8m³ Tranformer

Item No.	Description	Position	Item No.	Description	Position	Item No.	Description	Position
AC744	Rail JMV35SL 7 Hole 173mm for 59006	1	15772	Contactor 24Vac for 59006	4	35307	Fuse Keram.5x20 2.5A Delay for 59006	8
35305	End Fent for 59006	2	65708	Locking Plate Zap ZDU 6-2 for 59006	5	35323	End Plate Wire Connector for 59006	9
AI868	Mas AB100-K09KJ400 MS4P 24V 50/60Hz for 59006	3	35306	Fuse Clamp 2.5-2/ZSI for 59006	7	35315	Double Clamp 2.5-2 for 59006	10

Control Panel

Item No.	Description	Position	Item No.	Description	Position
AI879	Control Panel Small-PCB 1-Program for 59006	1	35413	Elbow 1/4 Int Brass for 59006	5
35579	Vacuum Meter 40mm for 59006	2	35414	Hose Pillar 1/4x4 BU R Norma for 59006	6